

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION –,– .
© COPYRIGHT – By – ALL RIGHTS RESERVED.


| LOC | DIST |
|---|---|
| H | — |

REVISIONS

| P | LTR | DESCRIPTION | DATE | DWN | APVD |
|---|---|---|---|---|---|
| | A | INITIAL RELEASE | 15MAR11 | RK | MKO |




NOTE:

1. HOUSING: GLASS FILLED THERMOPLASTIC
   CONTACTS: COPPER ALLOY
2. PLATING:
   CONTACT AREA: PERFORMANCE LEVEL 2 ACC. TO DIN 41612
   SOLDERING AREA: TIN OVER NICKEL
3. CONTACT ARRANGEMENTS:
   AN ASTERISK "X" DENOTES A SIGNAL CONTACT.
   AN ASTERISK "⊗" DENOTES KINKED A SIGNAL CONTACT.
4. KINKED POSTS
5. SOLDER POSTS SUITABLE FOR 1,0 NOM. P.C.B. HOLES
6. CONNECTOR PRINTED WITH PARTNUMBER AND DATECODE

3

| | | 1 2 3 4 5 6 7 8 9 10 11 12 13 14 15 16 17 18 19 20 21 22 23 24 25 26 27 28 29 30 31 32 |
|---|---|---|
| POS | | |
| ROW | c | ⊗ × × × × × × × × × × × × × × × × × × × × × × × × × × × ⊗ |
| | b | × × × × × × × × × × × × × × × × × × × × × × × × × × × × |
| | a | ⊗ × × × × × × × × × × × × × × × × × × × × × × × × × × × ⊗ |

| WITH | 2 | 1 | 2173047-4 |
|---|---|---|---|
| 4 | FINISH | MATERIAL | TE PARTNUMBER |

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ± –
1 PLC ± –
2 PLC ± –
3 PLC ± –
4 PLC ± –
ANGLES ± –

MATERIAL –
FINISH –

DWN RAVINDRA K 15MAR11
CHK MARCIN KOMAR 07APR11
APVD STEFAN HABERSTROH 07APR11
PRODUCT SPEC —
APPLICATION SPEC —
WEIGHT —

TE Connectivity

NAME
96P.IEC-C FEM.CONN.
ACC. DIN 41612 WITH SOLDER POSTS
2,4 – 3,2mm P.C.BOARD THICKNESS

| SIZE | CAGE CODE | DRAWING NO | RESTRICTED TO |
|---|---|---|---|
| A2 | 00779 | C-2173047 | — |

CUSTOMER DRAWING

| SCALE | SHEET | REV |
|---|---|---|
| NTS | 1 OF 1 | A |

2173047



Downloaded from Arrow.com.