










## Sockets

### BIL 20



Product	BIL 20
description	Socket with insulated head and ring for installation in equipment chassis and switchpanels with a wall thickness up to 2 mm. 4 mm diameter tin-plated zinc die-cast socket, with solder Connection and M6 thread.
operating instruction	BA403
article-no. / *colour	9301761xx <div>  00 black              01 red              02 blue              03 yellow              04 green              05 brown              06 gray              07 white              09 violet </div> <div>Sn</div>
drawing	
technical data	
connection	M6 thread, solder connection
rated voltage	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(2)</sup>
rated current (consider derating curve)	32 A
material socket	SKS_ZINKDRUCKGUSS-VERZINNT
housing material	PA
temperature range acc. To IEC61010 <sup>(1)</sup>	-25 °C to +85 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	V-2

<sup>(1)</sup> contact the manufacturer for applications at deviating temperature ranges

<sup>(2)</sup> without rated measurement category, for other circuits that are not directly connected to mains

stand: 24.08.2022

stand: 24.08.2022