



MICRO SWITCH

FREEPORT ILLINOIS, U.S.A.
A DIVISION OF HONEYWELL

FED. MFG. CODE 81929

SWITCH - BASIC

CATALOG LISTING

BZ-2R352420-A2

AGP7501

X200648-BZ

BZ-2R352420-A2

PAGE 1 OF 1

REPLACES

RELEASE NO ECO-0042359

M

DRAWING NUMBER

A

ISSUE

ASD


CHECK

REVISIONS

A	0042359
RVS	
07AUG68	

CHECK

CHECK



NOTE

- △ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF 1/32" MAX DIA ON 1.000 ± .002 CENTERS
- 2 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE	3 - 6 OZ
RELEASE FORCE	2.5 OZ MIN
DIFFERENTIAL TRAVEL	0004 - 0020
OVERTRAVEL	005 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT	S P D T
L95	
10A 125, 250 OR 480 VAC	
1/8HP 125 VAC, 1/4HP 250 VAC	

SCALE -

DO NOT SCALE PRINT

UNLESS OTHERWISE NOTED

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE (.0)	± .030
TWO PLACE (.00)	± .015
THREE PLACE (.000)	± .005
ANGLES	± -

WEIGHT .063 LB



FO-50378 RASTER DRAWN

CHECK

CHECK