

Product data sheet

Specifications



APC IT Power Distribution Module 3 Pole 4 Wire 50A CS50 440cm

PDM3450CS50-440

Overview

Presentation	Factory assembled and tested Power Distribution Modules include circuit breaker, power cord, power connection, and circuit monitoring. Auto-detection of modules by the Modular PDU minimizes installation time.
--------------	--

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 3 phases
Main Output Voltage	208 V 3 phases
Output connector type	CS50 1
Provided equipment	Installation guide

Physical

Colour	Black
Height	12.7 cm
Width	44.5 cm
Depth	40.6 cm
Net weight	4.45 kg

Input

Network frequency	60 Hz
Permissible voltage	200...240 V
Max line current	50 A

Output

Max current draw	50 A
Number of power socket outlets	1 CS50

Conformance

Product certifications	UL listed
------------------------	-----------

Packing Units

Unit Type of Package 1	Db
------------------------	----

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number of Units in Package 1	1
Package 1 Height	12.7 cm
Package 1 Width	40.6 cm
Package 1 Length	44.5 cm
Package 1 Weight	5 kg

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Under investigation
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
Take-back	Take-back program available

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------

Recommended replacement(s)