



Search by part # or keyword

Products

Industries &
Solutions

Resources

TE Store

Sign In



Connectors > PCB Connectors > Wire-To-Board Connectors > Housings

3-292254-0

CT RELAY HDR ASSY 10P BLUE



AMP CT

TE Internal #: **3-292254-0**

TE Internal Description: **CT RELAY HDR ASSY 10P BLUE**

Connector System : **Wire-to-Panel**

Number of Positions : **10**

Centerline (Pitch) : **2 mm [.078 in]**

Number of Rows : **1**

Housing Color : **Blue**

[Similar Products](#) | [Digital Datasheet](#)

Compatible Parts & Tooling

Purchase items directly from TE.com

We are here to help!

Get in touch with our product experts.



CHAT WITH US



EMAIL US



CALL US

Documents

Features

Product Compliance

Product Drawings

CT RELAY HDR ASSY 10P BLUE

[CT RELAY HDR ASSY 10P BLUE](#) English

CAD Files

3D PDF

[3D_CVM_CVM_3-292254-0_D.pdf](#) 3D

Customer View Model

[ENG_CVM_CVM_3-292254-0_D.2d_dxf.zip](#)

English

[ENG_CVM_CVM_3-292254-0_D.3d_igs.zip](#)

English

[ENG_CVM_CVM_3-292254-0_D.3d_stp.zip](#)

English

Datasheets &
Catalog Pages

2.0MM_AMP_CT_CONNECTOR_SERIES_QUICK_REF_GUIDE

[ENG_DS_1-1773455-8_CT_CONNECTOR_SERIES_QRG_0414_1-1773455-8_AMP_CT_Connector_Series.pdf](#) English

Product
Specifications

AMP COMMON TERMINATION (CT), CONNECTOR, 2mm PITCH, M/T TYPE, LEAD FREE VERSION

[JPN_SS_108-60016-1_C.tif](#) Japanese

Product Specification

[JPN_SS_108-60016-1_C.pdf](#) Japanese



Please review product documents or contact us for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.	
Product Type Features	Connector System : Wire-to-Panel Sealable : No
Configuration Features	Number of Positions : 10 Number of Rows : 1
Contact Features	Contact Base Material : Brass Contact Type : Pin Contact Retention Within Housing : Without Contact Current Rating (Max) (A): 4
Mechanical Attachment	Mating Retention Type : Locking Latch Panel Mount Feature Type : Latches Panel Mount Feature : With Mating Retention : With Connector Mounting Type : Panel
Housing Features	Housing Material : Nylon 66 Centerline (Pitch) : 2 mm [.078 in] Housing Color : Blue
Dimensions	Connector Width : 6 mm [.236 in] Connector Height : 12 mm [.472 in]
Usage Conditions	Operating Temperature Range : -40 – 105 °C [-40 – 221 °F]
Operation/Application	Circuit Application : Signal
Industry Standards	UL Flammability Rating : UL 94V-0 Approved Standards : UL Recognized
Packaging Features	Packaging Method : Bag/Box Packaging Quantity : 300
Statement of Compliance	Statement of Compliance pdf

Products with Similar Specs

[View All Similar Products](#)

WIRE-TO-BOARD CONNECTOR... 3-292254-0 CT RELAY HDR ASSY 10P BLUE  Non-Stocked Connector System : Wire-to-Panel Number of Positions : 10 Centerline (Pitch) : 2 mm Number of Rows : 1 Housing Color : Blue	WIRE-TO-BOARD CONNECTOR... 5-292254-0 CT RELAY HDR ASSY 10P YELLOW  Non-Stocked Connector System : Wire-to-Panel Number of Positions : 10 Centerline (Pitch) : 2 mm Number of Rows : 1 Housing Color : Yellow	WIRE-TO-BOARD CONNECTOR... 1-292254-0 CT RELAY HDR ASSY 10P NAT  In-Stock Connector System : Wire-to-Panel Number of Positions : 10 Centerline (Pitch) : 2 mm Number of Rows : 1 Housing Color : Natural	WIRE-TO-BOARD CONNECTOR... 7-292254-0 CT RELAY HDR ASSY 10P BLACK  Non-Stocked Connector System : Wire-to-Panel Number of Positions : 10 Centerline (Pitch) : 2 mm Number of Rows : 1 Housing Color : Black
---	--	--	--

Also in the Series | [AMP CT](#)

 PCB Connector Mounting (46)	 Wire-to-Board Connector Contacts (8)	 Wire-to-Board Connector Housings (226)	 Wire-to-Board Headers & Receptacles (753)
---	---	--	--