




Part Number : [1301270007](#)
Product Description : Super-Safeway
Receptacle Tension Tester and Receptacle
Tension Tester in Carrying Case
Series Number : 130127
Status : Active
Product Category : Wiring Devices
Engineering Number : 1760



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	130127
Description	Super-Safeway Receptacle Tension Tester and Receptacle Tension Tester in Carrying Case
IP Rating	N/A
NEMA Configuration	NEMA 1-15, NEMA 5-15, NEMA 5-20
Product Name	Super-Safeway
Specialty	Testing
Type	Tool Ground Continuity Tester
UPC	78678875295

Electrical

Current - Maximum per Contact	N/A
GFCI	No
Voltage - Maximum	N/A

Physical

Cord Type	N/A
Flange	No
Flip Lid	No
Gender	Male
Length	N/A
Lighted Connector	No
Locking Blade	N/A
Net Weight	75.630/g
Poles	N/A
Receptacle Type	N/A

This document was generated on Apr 17, 2025