
Data Sheet | Item Number: 706-7753/304-200

System cable; for WAGO-I/O-SYSTEM, 750 Series; 2 x 8 analog inputs or outputs; Length: 2 m; Conductor cross-section: 0.14 mm²

https://www.wago.com/706-7753/304-200





Similar to illustration

Color coding acc. to DIN VDE 47100 Cable 1; Channel 1-8		14 poles flat connector		20 poles flat connector	
		Pin number	Wiring	Pin number	Signal
White		1	CH1	1	DO1
Brown		2	CH2	2	DO2
Green		3	CH3	3	DO3
Yellow		4	CH4	4	DO4
Grey		5	CH5	5	DO5
Pink		6	CH6	6	DO6
Blue		7	CH7	7	DO7
Red		8	CH8	8	DO8
Black		9	+24V	17	+24V
Violet		10	0V	18	0V

Color coding acc. to DIN VDE 47100 Cable 2; Channel 9-16		14 poles flat connector		20 poles flat connector	
		Pin number	Wiring	Pin number	Signal
White		1	CH9	9	DO9
Brown		2	CH10	10	DO10
Green		3	CH11	11	DO11
Yellow		4	CH12	12	DO12
Grey		5	CH13	13	DO13
Pink		6	CH14	14	DO14
Blue		7	CH15	15	DO15
Red		8	CH16	16	DO16
Black		9	+24V	19	+24V
Violet		10	0V	20	0V

Short description:

WAGO's Interface Cables provide fast and easy connection of WAGO I/O Modules equipped with a 20-pole pluggable connector. The following WAGO I/O Modules and Interface Adapters are compatible:

- 750-1500 (16 DO) -- > 857-981 (DO)
- 750-1502 (8 DO/8 DI) --> 857-981 (DO) and 857-982 (DI)
- The cables are available in 1-, 2- and 3-meter lengths; each has one 20-pole or two 14-pole pluggable connectors at both ends.
- They are suitable for system wiring when paired with 857-981 and 857-982 Interface Adapters.

Notes

Note	When using more than 10 wires, the maximum current per wire must be reduced to 0.7 A.

Downloaded from Arrow.com.

Electrical data

Inputs/outputs	2 x 8 analog inputs or outputs
Operating voltage	≤ 35 VAC/VDC
Current per wire (max.)	1 A

Connection Data

Cable type	LiYY
Color code	per DIN VDE 47100

Connection 1

Pluggable connector	Pluggable connector per DIN 41651; female connector
Pole number 1	20
Connection type	System
Wire cross-section	0.14 mm²

Connection 2

Connector	Pluggable connector per DIN 41651; female connector
Pole number	14
Connection type	System
Wire cross-section	0.14 mm²

Connection 3

Connector	Pluggable connector per DIN 41651; female connector
Pole number	14
Connection type	System
Wire cross-section	0.14 mm²

Physical data

Cable length	2 m

Material data

Weight	181 g

Environmental requirements

Ambient temperature (operation)	-20 … +50 °C

Commercial data

Product Group	30 (WAGO France)
PU (SPU)	1 pcs
Packaging type	Box
Country of origin	FR
GTIN	4050821034186
Customs tariff number	85444290900

Product Classification

UNSPSC	26121604
eCl@ss 10.0	27-06-03-11
eCl@ss 9.0	27-06-03-11
ETIM 9.0	EC000237
ETIM 10.0	EC000237
ECCN	NO US CLASSIFICATION

Downloaded from Arrow.com.

Environmental Product Compliance

RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 706-7753/304-200

Documentation

Bid Text

706-7753/304-200	26.11.2018	docx 15.26 KB
706-7753/304-200	19.02.2019	xml 3.97 KB

CAD/CAE-Data

CAE data

WSCAD Universe 706-7753/304-200

1 Compatible Products

1.1 Optional Accessories

1.1.1 Interface module

1.1.1.1 Interface adapters



Item No.: 857-981
Interface adapter; 14-pole; High-side switching input



Item No.: 857-982
Interface adapter; 14-pole; High-side switching output

Downloaded from Arrow.com.