

Part Number : 5600201F



5600201F



This is a
RoHS Compliant Product
[To learn more click here](#)

General Description

Series	560
Configuration	Bi-Pin LED Lamp
Description	Bi Pin LED Lamp
Package Options	25 Pieces Per Bag
Sizes	5mm
Lamp Type	Single Color
Viewing	Top View
Polarity	Cathode Short Lead
Lens Style	Diffused
Viewing Angle	50

Absolute Maximum Ratings (Ta = 25°)

Forward Current mA	40mA
Reverse Voltage	5
Solder Temperature	260° for 5 sec
Operating Temperature	-55 to +100
Storage Temperature	-55 to +100

Operating Characteristics

LED Type	Resistor
Color	Green 
Luminous Intensity Min	4.5mcd
Luminous Intensity Typical	5.8mcd
Luminous Intensity Max	7.1mcd
Test Current mA	10mA
Emitted Color	Green
Dominant Wavelength Min	570nm
Power Dissipation Max	130mW

Related Products

4500521927012