





MICRO SWITCH
a Honeywell Division

FED. MFG. CODE 91929

MINIATURE PRECISION LIMIT SWITCH

CATALOG LISTING
914CE18-12



NOTES
1 - ZINC HOUSING FINISHED WITH GRAY PAINT

ANSI Y14.5M-1982 APPLIES

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	DO NOT SCALE PRINT
OPERATING FORCE — — — — 5 LB MAX		CONTACT ARRANGEMENT S P D T		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
DIFFERENTIAL TRAVEL — — — .004 MAX					
OVERTRAVEL — — — — — .118 MIN		5A 1/10HP 125 OR 250 VAC  		ONE PLACE (.0)	± .030
				TWO PLACE (.00)	± .015
				THREE PLACE (.000)	± .005
				ANGLES	±
				WEIGHT	

914CE18-12

M

DRAWING
NUMBER

2

ISSUE

REPLACES

RELEASE NO. PR-17295

CHECK

REVISIONS
A CO-69061
S A V
4 OCT 91

CHECK

14 NOV 91

2

CHECK

4 OCT 91

CHECK

DDM/CAD
DRAWN