Part Number : 1300180207
Product Description : Mini-Change 4 Pole 90° Adapter, Female to Male
Series Number : 130018
Status : Active
Product Category : Industrial Tees and Splitters
Engineering Part Number : 41212



Documents and Resources

Drawings

1300180207_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

Downloaded from Arrow.com.

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Industrial Tees and Splitters
Series	130018
Description	Mini-Change 4 Pole 90° Adapter, Female to Male
IP Rating	IP67
Product Name	Mini-Change
Type	Drop Tee
UPC	78678841212

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	8.0A
Voltage - Maximum	600V AC/DC

Physical

Color - Cable Jacket	Yellow
Drop Connector	Mini-Change
Drop Gender	Male
Keyway	Single
LED Indicator	None
Left Trunk Connector	Mini-Change
Left Trunk Gender	Female
Leg 1 Length	N/A
Leg 2 Length	N/A
Length	0.066m

Downloaded from Arrow.com.

Material - Cable Jacket	N/A
Material - Connector Body	PVC
Material - Coupling Nut	Zinc Die-Cast
Poles	4
Right Trunk Connector	N/A
Right Trunk Gender	N/A
Temperature Range - Operating	-20° to +80°C

Downloaded from Arrow.com.