



**Part Number :** [5040510901](#)

**Product Description :** 1.50mm Pitch, Pico-Lock Receptacle Crimp Housing, Single Row, Positive Lock, 9 Circuits, Black

**Series Number :** 504051

**Status :** Active

**Product Category :** Connector Housings



---

## Documents and Resources

### Drawings

[5040510901\\_sd.pdf](#)

### 3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

[5040510901.dxf](#)

### Specifications

[AS-504051-001-001.pdf](#)

[SPK-504051-001-001.pdf](#)

[5040510000-PS-000.pdf](#)


[5040511001-PS-000.pdf](#)

[PS-504051-001-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)

EU RoHS

Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of ComplianceAdditional Product Compliance Information**Part Details****General**

Status	Active
Category	Connector Housings
Series	504051
Description	1.50mm Pitch, Pico-Lock Receptacle Crimp Housing, Single Row, Positive Lock, 9 Circuits, Black
Application	Signal, Wire-to-Board
Comments	See Molex product specification PS-504051-001 for additional current de-rating information
Keyword	Pico-Lock 1.5
Product Name	Pico-Lock
UPC	191128805117

**Agency**

CSA	LR19980
UL	E29179

## Physical

Circuits (maximum)	9
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	High Temperature Thermoplastic
Net Weight	100.100/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
1.50mm Pitch Pico-Lock Right-Angle Single Row Headers	<u>504050</u>

### Use with Part(s)

Description	Part Number
1.50mm Pitch Pico-Lock Female Crimp Terminals	<u>504052</u>

---

This document was generated on May 04, 2026