

Eaton SPOD420STR

Catalog Number: SPOD420STR

Eaton Bussmann series SPOD surgePOD module, Optional remote contact signaling, SurgePOD module, 200 Kilo Ampere, Nickel-plated copper, 420 V - SPOD420STR

General specifications

Product Name	Catalog Number
Eaton Bussmann series SPOD surgePOD module	SPOD420STR
	UPC
	051712393836
Product Length/Depth	Product Height
.001 in	.001 in
Product Width	Product Weight
.001 in	.1 lb
Warranty	Compliances
5 year	Contact factory RoHS Compliant
Certifications	
UL 94V0 UL Listed	



Product specifications

Short-circuit rating

200 kA

Special features

Optional remote contact signaling

Accessories

Standard module

Type

SurgePOD module

Operating temperature

-25 to 85 °C

Material

Nickel-plated copper

Maximum continuous operating voltage

420 V

Nominal Discharge Current

20 kA

Resources

Catalogs

[Eaton's Volume 3—Power Distribution and Control Assemblies](#)

Specifications and datasheets

[Eaton Specification Sheet - SPOD420STR](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)