

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1301140019

Status:

Active

Overview:

Lighting Accessories

Description:

Incandescent Stringlight Construction Guard 1-3/4 Neck Zinc Plated, Long, Narrow Profile



Documents:	
Brochure (PDF)	RoHS Certificate of Compliance (PDF)
General	
Product Family	Portable Lighting
Series	130114
NEMA Configuration	N/A
Outlet	N/A
Overview	Lighting Accessories
Product Name	Woodhead
Type	Accessory
UPC	78678861178
Physical	
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	120.65mm (4.750")
Duty	Industrial
Guard Included	Yes
Guard Type	Steel
Height	241.30mm (9.500")
Length	N/A
Material - Guard	#8 Gauge Zinc-plated Steel
Net Weight	195.040/g
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	N/A
Lamp Type	PS30
Lamp Wattage - Maximum	N/A
On/Off Switch	N/A
Voltage (Fixture) - Maximum	N/A
Material Info	
Engineering Number	378

EU ELV	
Not Reviewed	
EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

130114 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION