

**Part Number :** [1301540064](#)

**Product Description :** Super-Safeway Standard Molded Y Cordset, 2 Pole/3 Wire SOOW Cordset, Cordset Length 0.91m (3.0'), NEMA L5-20, 125V

**Series Number :** 130154

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 2647-Y



---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130154
Description	Super-Safeway Standard Molded Y Cordset, 2 Pole/3 Wire SOOW Cordset, Cordset Length 0.91m (3.0'), NEMA L5-20, 125V
IP Rating	N/A
NEMA Configuration	NEMA L5-20
Product Name	Super-Safeway
Specialty	N/A
Type	Molded Y Cordset
UPC	78678800620

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	0.91m (3.0')
Lighted Connector	No
Locking Blade	Yes
Net Weight	1.000/g
Poles	2-pole/3-wire
Receptacle Type	Duplex

---

This document was generated on Jun 07, 2026