

## Han A Hood Side Entry LC 4 Pegs M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 20 032 1521
Specification	Han A Hood Side Entry LC 4 Pegs M25
HARTING eCatalogue	<a href="https://b2b.harting.com/19200321521">https://b2b.harting.com/19200321521</a>

### Identification

Category	Hoods/Housings
Series of hoods/housings	Han A <sup>®</sup>
Type of hood/housing	Hood
Type	Low construction

### Version

Size	32 A
Version	Side entry
Cable entry	1x M25
Locking type	Double locking lever
Field of application	Standard Hoods/housings for industrial applications

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 4X 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 7037 (dust grey)



Pushing Performance  
Since 1945

## Material properties

RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R1 (HL 1-3) R7 (HL 1-3)

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	195.4 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140124950
ETIM	EC000437
eCl@ss	27440202 Shell for industrial connectors