Part Number : 1301430238
Product Description : Watertite Extreme Cordset, 12 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 15.24m (50.0'), NEMA L14-20, 250V
Series Number : 130143
Status : Active
Product Category : Wiring Devices
Engineering Part Number : 26W74B124



Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Relevant
EU RoHS	Not Relevant

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

Downloaded from Arrow.com.

General

Status	Active
Category	Wiring Devices
Series	130143
Description	Watertite Extreme Cordset, 12 Gauge SOOW, 3 Pole/4 Wire, Cordset, Length 15.24m (50.0'), NEMA L14-20, 250V
IP Rating	IP69K
NEMA Configuration	NEMA L14-20
Product Name	Watertite Extreme
Specialty	N/A
Type	Cordset
UPC	78678871256

Agency

CSA	LR6837
UL	E38085

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	250V

Physical

Cord Grip Body Size	F3 3/4"
Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	15.24m (50.0')
Lighted Connector	No
Locking Blade	Yes
Net Weight	5485.000/g
Poles	3-pole/4-wire
Receptacle Type	Single

Downloaded from Arrow.com.

Downloaded from Arrow.com.