

Specification Sheet

Part Number: 157-00373



All-in-one bundling and fastening solution reduces costs and assembly time.

Disc feature provides anti-rattle protection in high-vibration applications.

1-Piece Cable Tie with Fir Tree Mount with Disc, 0.24 - 0.27" Mounting Hole, 50lb, PA66HIRHSUV, Black, 500/pkg

Article Number 157-00373

Type T50SOSFT6.5LG-E4

Color Black (BK)

Quantity Per pack

Product Description One-piece mounting ties offer a complete solution by both bundling and mounting wires, cables and tubes. The fir tree mount provides low insertion force with a high extraction force. Outside serrations on the cable tie leave a smooth interior surface that's gentler on sensitive wire insulation. The unique head design allows the cable tie to firmly hold bundles as small as .06" diameter. The disc offers added protection against debris.

Short Description 1-Piece Cable Tie with Fir Tree Mount with Disc, 0.24 - 0.27" Mounting Hole, 50lb, PA66HIRHSUV, Black, 500/pkg

Global Part Name	T50SOSFT6.5LG-E4-PA66HIRHSUV-BK
------------------	---------------------------------

Minimum Tensile Strength (Imperial)	50
-------------------------------------	----

Minimum Tensile Strength (Metric)	225
-----------------------------------	-----

Length L (Imperial)	6.6
---------------------	-----

Length L (Metric)	167.9
-------------------	-------

Fixation Method	Fir tree for round holes
-----------------	--------------------------

Identification Plate Position	none
-------------------------------	------

Releasable Closure	No
--------------------	----

Tie Closure	plastic pawl
-------------	--------------

Width W (Imperial)	0.18
--------------------	------

Width W (Metric)	4.6
------------------	-----

Bundle Diameter Min (Imperial)	0.04
--------------------------------	------

Bundle Diameter Min (Metric)	1.0
------------------------------	-----

Bundle Diameter Max (Imperial)	1.38
--------------------------------	------

Bundle Diameter Max (Metric)	35.0
------------------------------	------

Thickness T (Imperial)	0.05
------------------------	------

Thickness T (Metric)	1.3
Height H (Imperial)	0.05
Height H (Metric)	1.3
Panel Thickness Min (Imperial)	0.02
Panel Thickness Max (Imperial)	0.32
Panel Thickness Min (Metric)	0.6
Panel Thickness Max (Metric)	8.25
Mounting Hole Diameter D (Imperial)	0.24 - 0.27 "
Mounting Hole Diameter D (Metric)	6.1 - 6.9 mm
Mounting Hole Diameter D Min (Imperial)	0.24
Mounting Hole Diameter D Max (Imperial)	0.27
Mounting Hole Diameter D Max (Metric)	6.9
Disc Diameter (Metric)	16.0
Disc Diameter (Imperial)	0.63
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Use Conditions	For Indoor and Outdoor Use
Operating Temperature	-40°F to +221°F (-40°C to 105°C, +125C, 5000 h; 160C, 1000h; 165C, 500h per ITS 0019)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)