





REV.	ECR/ECN No.	DESCRIPTION	DRAWN/DATE	CHECKED/DATE	APPROVED/DATE
A	/	Initial version	Wenhong Liu 2022-11-15	SH.Chen 2022-11-15	Rain.Han 2022-11-15



A TYPE



B TYPE



PART NUMBER:

FF5026-A****-***

No. of Pin


Total Length of FFC

S:The contact surface is on the same side

O:The contact surface is on the opposite side

Structure				
No.	Item	Specification		Remark
①	Insulation	White 65um 125C 60V	PET	
②		White 65um 125C 60V		
③	Supporting Tape	218um	PET	
④	Conductor (Tin plated copper)	Thickness	0.035	±0.005
		Width	0.3	±0.03
⑤	Conductor Plating	Plated	Sn(1um)	Min
		Plated		

Dimension 尺寸		
Item	项目	Specification
NO. of conductors	导体芯数	N **
Pitch	间距	P 1.0±0.08
Total Pitch	总间距	SP P*(N-1)±0.08
Total Length	总长度	TL ***±2.0
Insulation Length	绝缘长度	IL ***±2.0
Margin Width	边距	M 1.0±0.1
Total Width	总宽度	W P*(N+1)±0.08
Strip Length	金型长度	S1 **±0.5
Strip Length	金型长度	S2 **±0.5
Reinforeing tape length	补强板长度	B1 **±1.0
Reinforeing tape length	补强板长度	B2 **±1.0
Slanting	线口倾斜度	A ≤0.3
Terminal thickness	插入厚度	T 0.31±0.03
Thickness insulation	线身厚度	ST 0.16±0.05

Special request		UNLESS OTHERWISE SPECIFIED TOLERANCES				ANGLE OF PROJECTION		 Amphenol Aorora Technology (Huizhou) Co.,Ltd					
1.Storage of FFC: Temperature: 10~35℃ Humidity:30~65%RH 2.Periods: FFC(Plating Au)12months FFC(Plating Sn)6months 3.All material must be complied with RoHS 4.Temperature resistance requirements: -40~125℃		X.	±0.30	X. °	± 5'			DOC TYP Customer Drw		TITLE: FFC Cable P1.0mm L****mm ***pin			
		X.X	±0.25	X.X °	± 4'								
		X.XX	±0.20	X.XX °	± 3'	DRAWN	DATE	Wenhong Liu 2022-11-15	SIZE A4	PART NUMBER: FF5026-A****-****		REV. A	
		X.XXX	±0.15	X.XXX °	± 2'	DESIGN	DATE	Wenhong Liu 2022-11-15					
		LINEAR DIMS		ANGLES DIMS		CHECKED	DATE	SH.Chen 2022-11-15					
DWG NO.: A-NXXXX		MATERIAL		SEE NOTES		APPROVED	DATE	Rain.Han 2022-11-15	SCALE		1:1	UNIT : mm	SHEET 1 OF 1
FINISHED		SEE NOTES											