© – TE Connectivity. All Rights Reserved.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GO TO PRODUCTION (ECN-26-392024)	06JUL2026	YS	AM

NOTES :


1. ALL DIMENSIONS ARE NOMINAL FOR REFERANCE ONLY UNLESS OTHERWISE STATED;
2. ROHS: COMPLIANT


MATERIALS AND PLATING		UNIT: MICRO-INCHES
PART NAME	MATERIALS	PLATING
BODY	BRASS HBi 59-1	ALBALOY 100u"/NI-P(9-12wt%) 100u"
INSULATOR	PTFE ASTM-D-1710	N/A
CONTACT PIN	Be-Cu C17200	GOLD 3u"/NI-P(9-12wt%) 100u"/COPPER 50u"


ELECTRICAL CHARACTERISTICS		
IMPEDANCE		50 Ω
VOLTAGE RATING		335V(rms)
FREQUENCY RANGE		DC~18 GHz
DIELECTRIC WITHSTANDING VOLTAGE		>750 V
CONTACT RESISTANCE	CENTER CONTACT	<3.0 mΩ
	OUTER CONTACT	<2.5 mΩ
INSULATION RESISTANCE		>5000 MΩ
INSERTION LOSS		N/A
VSWR		< 1.40

MECHANICAL CHARACTERISTICS	
FORCE TO ENGAGE AND DISENGAGE	N/A
CENTER CONTACT RETENTION FORCE	>6 lbs
RECOMMENDED COUPLING TORQUE	N/A
COUPLING NUT RETENTION FORCE	N/A
DURABILITY	>500cycles

ENVIRONMENTAL PARAMETER	
TEMPERATURE RANGE	-40 ℃~+125 ℃
CORROSION	MIL- STD 202, Meth. 101,Cond. B
THERMAL SHOCK	MIL- STD 202, Meth. 107,Cond. B
Vibration	MIL-STD-202,Method 204,Cond D
Shock	MIL-STD-202,Method 213,Cond I







Pb < 1000 PPM

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± –
1 PLC	± 0.3
2 PLC	± 0.2
3 PLC	± 0.1
4 PLC	± –
ANGLES	± –

MATERIAL: –

FINISH: –

DWN	26FEB2026 SARGUNAM, YAZHINI
CHK	26FEB2026 DAI, ERIC
APVD	26FEB2026 ZI, WILL
PRODUCT SPEC	—
APPLICATION SPEC	—
WEIGHT	0

TE Connectivity

NAME: QMA FEMALE R/A FOR PCB MOUNTING,50Ω

–

–


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2547895	—

CUSTOMER DRAWING | SCALE 1:1 | SHEET 1 OF 2 | REV A

Downloaded from Arrow.com.

© – TE Connectivity. All Rights Reserved.


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	–	SEE SHEET 1	–	—	—




NOTE:
1. 1PCS/BAG ;
2. 50 BAG/BOX=50PCS/BOX ;
3. 10 BOX/CARTON=500PCS/CARTON
4. BAG TEXTURE : PE ;
5. BOX/CARTON TEXTURE : CORRUGATED BOARD ;
6. SINGLE WEIGHT : 2.56G ;
7. WEIGHT PER BOX : 3630G ;
8. THE PACKAGING INFORMATION IS APPLICABLE TO: 2557895-1



1 PCS / BAG
STICK A LABEL ON THE BAG



10 BOX / CARTON
STICK A LABEL ON THE CARTON



50 PCS / BOX
STICK A LABEL ON THE BOX

10 BOX

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 26FEB2026 SARGUNAM, YAZHINI	TE Connectivity
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± – ; 1 PLC ± 0.3 ; 2 PLC ± 0.2 ; 3 PLC ± 0.1 ; 4 PLC ± – ; ANGLES ± –	CHK 26FEB2026 DAI, ERIC	NAME QMA FEMALE R/A FOR PCB MOUNTING,50 – –
		APVD 26FEB2026 ZI, WILL	
		PRODUCT SPEC —	SIZE A3 / CAGE CODE 00779 / DRAWING NO C-2547895 / RESTRICTED TO —
		APPLICATION SPEC —	
MATERIAL –	FINISH –	WEIGHT 0	SCALE 1:1 / SHEET 2 OF 2 / REV A
		CUSTOMER DRAWING	

Downloaded from Arrow.com.