



Part Number : [197084003](#)
Product Description : PCB Tab Quick Disconnect,
Male, for Wire, Metal Strip, Tab 4.75 x 0.51mm
Series Number : 19708
Status : Active
Product Category : Quick Disconnects



Documents and Resources

Drawings

[197084003_sd.pdf](#)
[PK-19511-601-001.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[PS-19708-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Quick Disconnects
Series	19708
Description	PCB Tab Quick Disconnect, Male, for Wire, Metal Strip, Tab 4.75 x 0.51mm
Product Name	PCB Tab
Type	PCB Tab
UPC	800754886840

Agency

UL	E79133
----	--------

Electrical

Voltage - Maximum	N/A
-------------------	-----

Physical

Barrel Type	N/A
Gender	Male
Glow-Wire Capable	No
Insulated	No
Insulation	None
Lock to Mating Part	No

Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.541/g
Orientation	PCB Straight Tab
Packaging Type	Reel
Plating min - Mating	3.810µm
Plating min - Termination	3.810µm
Polarized to Mating Part	No
Tab Thickness	0.51mm
Tab Width	4.75mm
Wire Insulation Diameter	N/A
Wire Size (AWG)	N/A

This document was generated on May 20, 2026