





VALIDATED ACCORDING: GMI 12590
GEPRUEFT NACH: GMI 12590

NEUTRAL VERSION

DCSI 9.5MM FEMALE TERM.	6 007 02 71	10763018	>6.00 - 10.00	Ø 5.80 - Ø 6.60	6 099 33 03	10721071	3, 5
				Ø 5.40 - Ø 6.60	6 099 33 04	10889241	
				Ø 3.50 - Ø 5.50	6 099 33 01	15327788	
	6 007 02 61	15327734	>4.00 - 6.00	Ø 3.40 - Ø 4.40	6 099 33 08	13546490	
				Ø 3.50 - Ø 5.50	6 099 33 01	15327788	
				6 007 02 51	10775312	>2.50 - 4.00	
Ø 3.40 - Ø 4.40	6 099 33 08	13546490					
DCSI 6.3MM FEMALE TERM.	6 004 00 51	10748126	4.00	Ø 3.10 - Ø 5.50	6 099 26 06	12186636	1, 2
	6 004 00 41	15340695	1.50 - 2.50	Ø 2.20 - Ø 3.20	6 099 26 04	15443869	
	6 004 00 31	12186637	0.50-0.75-1.00	Ø 1.40 - Ø 2.30	6 099 26 07	12186638	
DCSI 2.8MM FEMALE TERM.	6 004 05 41	33511768	>1.00 - 1.50	Ø 2.20 - Ø 2.70	6 099 34 05	33501746	6, 7, 8, 9
	6 001 05 31	12198447	0.50 - 1.00	Ø 1.70 - Ø 2.10	6 099 34 03	15327786	
	6 001 05 11	15395924	0.35	Ø 1.20 - Ø 1.60	6 099 34 01	33511807	
DESCRIPTION	MVL	DELPHI	WIRE SIZE DRAHTGROSSEN- BEREICH (mm ²)	ISOLATION SIZE ISOLATIONSBEREICH (Ø)	MVL	DELPHI	CAVITY-NO. KAMMER-NR.
	PART-NO. TEILE-NR.				PART-NO. SINGLE WIRE SEAL Einzeladerdichtung		
USEABLE TERMINALS FOR THIS CONNECTOR GEEIGNETE KONTAKTE FUER DIESEN STECKER							

13-00711		A5	DPN 33511769 REPLACED BY 33511807			
ECN-NO. ECN-NUMBER		POSITION POSITION		CHANGE DESCRIPTION ÄNDERUNGSBESCHREIBUNG		
PRODUCT SPEC. PRODUKT-SPEZ.		PACKAGING SPEC. VERPACKUNGS-SPEZ.		APPLICATION SPEC. ANWENDUNGS-SPEZ.		COPYRIGHT DELPHI CORPORATION AND/OR ITS AFFILIATES. ALL RIGHTS RESERVED. REVISÉ PATENT DRAUING IS THE PROPERTY OF DELPHI CORPORATION AND CONTAINS DELPHI CONFIDENTIAL INFORMATION. THE REPRODUCTION, DISTRIBUTION AND UTILIZATION OF THIS DOCUMENT OR ITS RELATED CAD DATA, AS WELL AS COMMUNICATION OF ANY CONTENT TO OTHERS, WITHOUT EXPRESS AUTHORIZATION, IS PROHIBITED. DIESE ZEICHNUNG IST EIGENTUM VON DELPHI CORPORATION UND ENTHÄLT VERTRAULICHE INFORMATIONEN VON DELPHI CORPORATION. Vervielfältigung, Verbreitung und Nutzung dieses Dokuments oder dessen inhalte, ODER AUCH IKS-KOMPAKTION VON BEZIEHUNGS PARTNERN ZU ANDEREN, IST OHNE BEGLEITENDES FREIGABESTEUERUNG DURCH DIE DELPHI CORPORATION UNTERSAGT.
				9 902 07 40		
TOLERANCES TOLERANZEN		DIN ISO 2768 M1 DIN ISO 2768 M2		MATERIAL : MATERIAL : SEE TABLE SIEHE TABELLE		 DELPHI PACKARD ELECTRICAL/ELECTRONIC ARCHITECTURE NÜRNBERG, GERMANY  ISO PROJECTION DIMENSION IN MILLIMETERS BEMESSUNG IN MILLIMETER
COUNTERPART No. GEGENSTÜCK-NR.:		SEE NOTES		COLOUR : FARBE :		
DO NOT MEASURE DRAWING ZEICHNUNG NICHT VERMESSEN		DATE DATUM		NAME NAME		 ECO Loc. Code STANDORT CODE GN
		1996-05-19		WEL		
CREATED BY ERSTELLT		1996-05-19		WEL		DRAWING NUMBER ZEICHN.-NUMMER
MODIFIED BY GEÄNDERT		20130619		M WELTHER		
CHECKED BY GEPRÜFT		20130619		M SCHINDHELM		STATE STATUS
APPROVED BY FREIGABEST.		20130619		Olat HOIERN		
FILE NAME DOK.-NAME		60431011C				PART NUMBER TEILENUMMER
						REV. INDEX
						SCALE MASSSTAB
						60431011C SERIAL RELEASED 60431011 A
						2:1