

Representative Image

Catalog No. GSB219

Description: 2-PC INNER SLVE CONN SLV I.D. 0.219

UPC No 786210813141

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Two Piece Inner Sleeve Connector for Hexagonal Range, Length 5/16 Inch/7.9mm, Inner Diameter .219 Inches/5.56mm, Outer Diameter .250 Inches/6.35mm, Color Silver, Hard Bronze, Tin Plated

Descriptors

Category	Electrical terminals
Special Features	Shielded cable grounding system made of 2 cylindrical sleeves (inner sleeve + outer sleeve), for solderless crimp connection. Inner sleeve for the Hexagonal Range (the corresponding outer sleeve is crimped with a hand tool and the result is a hexagonal-shaped crimp), for grounding shielded and coaxial cables. The sleeves are color coded according to their size. Millions of installations in communications, aerospace, electronic, telephone, radio and TV applications.

Specifications

Material	Hard Bronze
Color	Gray

Classifications

Brand Name	Sta-Kon
Sub Brand	Shield-Kon

Compliance and Certifications

RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant

ETIM	EC002650 Connection for screened wires
Model	2-part
Sleeve form	Internal sleeve
Insulated	N
Outer diameter sleeve	6.35 mm
Inner diameter sleeve	5.56 mm
Sleeve length	7.9 mm
Sleeve length	0.311 inch

Downloaded from Arrow.com.

ETIM	EC002650 Connection for screened wires
Colour code	Silver
Compression shape	Hexagon
Reel packaging	N

Downloaded from Arrow.com.