



Part Number : [192160011](#)

Product Description : Ultimate Wire Tap, Red, 22-18 AWG, 0.34 - .0.75mm², Carton

Series Number : 19216

Status : Active

Product Category : Splices

Engineering Part Number : WT-2218



Documents and Resources

Drawings

[192160011_sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)


[Creo](#)

Specifications

[PS-19902-013-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Splices
Series	19216
Description	Ultimate Wire Tap, Red, 22-18 AWG, 0.34 - .0.75mm ² , Carton
Product Name	Wire Tap
Type	Wire Tap
UPC	800753022133

Agency

CSA	LR18689
UL	E79133

Electrical

Voltage - Maximum	600V
-------------------	------

Physical

Barrel Type	Open
Color - Resin	Red
Flammability	94V-2
Insulation	Nylon
Material - Metal	Copper Alloy
Material - Plating Mating	Tin

Material - Plating Termination	Tin
Net Weight	1.130/g
Packaging Type	Carton
Temperature Range - Operating	105°C
Wire Size (AWG)	22, 20, 18
Wire Size mm ²	0.34-0.75

Mates With / Use With

Mates with Part(s)

Description	Part Number
Mates With	Male Quick Disconnect

This document was generated on May 27, 2026