

Part Number : [1301120104](#)

Product Description : 300W Guard Open-End with Reflector Yellow Vinyl Coating

Series Number : 130112

Status : Obsolete

Product Category : Portable Lighting Accessories

Engineering Number : 1165IG



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	Portable Lighting Accessories
Series	130112
Description	300W Guard Open-End with Reflector Yellow Vinyl Coating
NEMA Configuration	N/A
Product Name	Woodhead
Type	Accessory
UPC	78678846504

Electrical

Lamp Wattage - Maximum	N/A
Lumens	N/A
On/Off Switch	No
Voltage (Fixture) - Maximum	N/A

Physical

Bulb Type	N/A
Cord Length - Primary	N/A
Cord Length - Secondary	N/A
Depth	N/A
Duty	General
Guard Included	Yes
Guard Type	Insulated, Open End, Reflector, Steel
Height	N/A
Lamp Type	A23
Length	N/A
Material - Guard	#8 Gauge Vinyl Coated Steel
Outlet	None
Packaging Type	Carton