



Power Pack 1000 Terminals




- ◆ 145 amp capability
- ◆ Female terminal
 - 2 piece
 - Silver plated
 - BeCu contact insert
- ◆ Cable range 6 mm² – 25 mm²
- ◆ Inline and right angle female
 - 3 part numbers cover cable range
 - 6 total (3 inline, 3 right angle)
- ◆ Male terminal mates to inline or right angle female
 - 3 part numbers cover cable range



Picture	Production Part Number	Specifics:
	13675577	4.54 - 5.79 dia cable (8 - 10)
	13675578	6.63 - 8.13 dia cable (13 - 16)
	13675579	7.75 - 10.2 dia cable (19 - 25)
	13675583	4.54 - 5.79 dia cable, In-Line (8 - 10)
	13675584	6.63 - 8.13 dia cable, In-Line (13 - 16)
	13675585	7.75 - 10.2 dia cable, In-Line (19 - 25)
	13675587	4.54 - 5.79 dia cable, Right Angle (8 - 10)
	13675589	6.63 - 8.13 dia cable, Right Angle (13 - 16)
	13675590	7.75 - 10.2 dia cable, Right Angle (19 - 25)

DELPHI


Power Pack 1000 Connectors

Picture	Production Part Number (non-FR)	Production Part Number (FR)	Specifics:	High Volume Target PPAP (FR and non-FR materials)
	13849747	13842452	2W M In-Line, Index Right	1-Nov-12
	13849748	13842453	2W M In-Line, Index Left	1-Nov-12
	13849749	13842454	2W M Right Angle, Index Right	1-Nov-12
	13849750	13842455	2W M Right Angle, Index Left	1-Nov-12
	13849756	13842460	2W F In-Line, Index Right	1-Nov-12
	13849757	13842461	2W F In-Line, Index Left	1-Nov-12
	13849758	13842462	2W F Right Angle, Index Right	1-Nov-12
	13849759	13842463	2W F Right Angle, Index Left	1-Nov-12
	13849785	13842473	4.5 - 5.6 dia cable (red) Now Gray	PPAP
	13849786	13842474	5.6 - 6.9 dia cable (blue) Now Black	PPAP
	13849787	13842475	6.8 - 8 dia cable (natural) Now White	PPAP
	13849788	13842476	8 - 9.2 dia cable (black) Now Blue	PPAP
	13849789	13842477	9 - 10.2 dia cable (gray) Now Red	PPAP
	13959822	13959822	2W M In-Line, Index Right	1-Nov-13
	13959823	13959823	2W M In-Line, Index Left	1-Nov-13
	13959824	13959824	2W M Right Angle, Index Right	1-Nov-13
	13959825	13959825	2W M Right Angle, Index Left	1-Nov-13
	13952702	TBD	1W F In-Line, Index Right	PPAP
	TBD	TBD	1W F In-Line, Index Left	TBD
	TBD	TBD	1W F Right Angle, Index Right	TBD
	TBD	TBD	1W F Right Angle, Index Left	TBD
	13882980	TBD	1W M In-Line, Index Right	PPAP
	TBD	TBD	1W M In-Line, Index Left	TBD
	TBD	TBD	Right Angle, Index Right	TBD
	TBD	TBD	Right Angle, Index Left	TBD
	13675510	13675510	4.54 - 5.79 dia cable (gray)	PPAP
	13675511	13675511	5.4 - 6.6 dia cable (blue) Now Black	PPAP
	13675512	13675512	6.63 - 7.75 dia cable (brown) Now White	PPAP
	13675513	13675513	7.61 - 9.19 dia cable (green) Now Blue	PPAP
	13675514	13675514	9 - 10.2 dia cable (yellow) Now Red brown	PPAP

DELPHI

Power Pack 2000

Part number availability

Picture	Part Number	Gender	Description	Status
	13520916	F	ASM CONN 1 F PWR PACK 2000 SLD Index 0	LV PPAP'd
	13817281	F	ASM CONN 1 F PWR PACK 2000 SLD Index 1	Not PPAP'd
	13817280	F	ASM CONN 1 F PWR PACK 2000 SLD Index 2	Not PPAP'd
	13611153	F	ASM CONN 1 F PWR PACK 2000 SLD Index 3	LV PPAP'd
	13954995	F	CONN 1F PWR PACK 2000 SLD Right angle Index 0	15-Nov-12
	13948595	M	1W header mates with 13954995 Rt Angle Index 0	15-Nov-12
	13520386	M	1W header Mates with 13520916 Straight Index 0	LV PPAP'd
	13520909	M	CONN 1M PWR PACK 2000 SLD	LV PPAP'd
	15411422	N/A	SEAL CBL 1W; 19mm2	PPAP'd
	15411421	N/A	SEAL CBL 1W; 32mm2	PPAP'd
	15411420	N/A	SEAL CBL 1W; 50mm2	PPAP'd
	15411419	N/A	SEAL CBL 1W; 62mm2	PPAP'd
	13520911	N/A	Lock TPA PWR PACK 19mm2	PPAP'd
	13523148	N/A	Lock TPA PWR PACK 32mm2	PPAP'd
	13523149	N/A	Lock TPA PWR PACK 50mm2	PPAP'd
	13523150	N/A	Lock TPA PWR PACK 62mm2	PPAP'd
	15496986	F	TERM F PWR PACK 2000 SLD; right angle; 13mm2-19mm2	PPAP'd
	13513037	F	TERM F PWR PACK 2000 SLD; right angle; 32mm2	PPAP'd
	13513038	F	TERM F PWR PACK 2000 SLD; right angle; 40mm2-50mm2	PPAP'd
	13513039	F	TERM F PWR PACK 2000 SLD; right angle; 62mm2	PPAP'd
	13520912	F	TERM F PWR PACK 2000 SLD; inline; 13mm2-19mm2	PPAP'd
	13523152	F	TERM F PWR PACK 2000 SLD; inline; 32mm2	PPAP'd
	13523153	F	TERM F PWR PACK 2000 SLD; inline; 40mm2-50mm2	PPAP'd
	13523154	F	TERM F PWR PACK 2000 SLD; inline; 62mm2	PPAP'd
	13520914	M	TERM M PWR PACK 2000 SLD; 13mm2-19mm2	PPAP'd
	13523156	M	TERM M PWR PACK 2000 SLD; 32mm2	PPAP'd
	13523157	M	TERM M PWR PACK 2000 SLD; 40mm2-50mm2	PPAP'd
	13523158	M	TERM M PWR PACK 2000 SLD; 62mm2	PPAP'd
	Sonic Weld Version			
	13801592	F	TERM F PWR PACK 2000 SLD; right angle; 25mm2-50mm2	PPAP'd
	13815981	F	TERM F PWR PACK 2000 SLD; inline; 25mm2-50mm2	PPAP'd

DELPHI