



➤ PRODUCT NAVIGATOR

PRODUCTS | WEB-SHOP | DISTRIBUTION | DOWNLOAD | MARQUARDT GROUP | CONTACT

MARQUARDT WORLDWIDE



PRODUCTS

Rocker switches

Pushbutton switches

Toggle switches

Slide switches

Rotary switches

Foot switches

Tact and key switches

Snap-action switches

Micro-signal switches

ECO switches

Sensors

Systems and modules

Accessories

General information

Catalog request /
download

PRODUCTS ▶ ROCKER SWITCHES

Rocker switches

SERIES 1550 - SINGLE-POLE ROCKER SWITCHES - TO 16 (4) A 250 V AC

◀ Show previous product

Show next product ▶

1552.3102

Drawing



Similar to original
product

➔ Print data
sheet

Product number	1552.3102
Actuator color / printing	
Inrush current (capacitive)	100 A
Switching function	ON / OFF switch (DPST)
Number of poles	2-pole
connections	Quick-connect terminal, 6.3
Mechanical life endurance	5E4
Rating IEC	10 (4) A 250 V AC 5E4 16 (4) A 250 V AC 1E4
Rating North America	16 A 125 V AC 1 HP 16 A 250 V AC 2 HP
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm
Insulation resistance (new condition)	> 100 (500 V DC) MOhm
Proof tracking	250 PTI
Protection type	Connection IP 40
Ambient temperature	-20 °C ... +100 °C
Ambient temperature	-20 °C ... +55 °C
Flammability	UL 94 V-2
Glow wire test temperature	850 °C
Actuators and additional actuators	PA, black
Housing description	PA, black
Contact material	Ag
Contact distance	≥ 3 mm
Plug force of the terminals	≤ 80 N
Approval marks	CSA / UL / ENEC 05
Suitable for appliances of protection class	II
Shop / Stock version	

We reserve the right to make technical modifications and improvements to our products. Data in the catalog (e.g. dimensions, photos, diagrams) are not binding. Specifications, samples and installation drawings with tolerance data will gladly be provided on request.