





- **Extended length is with 500g of force**



P1		P2
1	WHITE	1
2	BLACK	2
3	RED	3
4	GREEN	4
5	YELLOW	5
6	BLUE	6

Extended Length ("L2")	Typical Retracted Length ("L1")
60.0 Inches - 69.0 Inches	21.5 Inches
1,524.0MM-1,752.6MM	546.1MM

Material:

- Plug Housing: Polycarbonate, clear
- Plug Terminal: 0.36"[0.14MM] Thick Phosphor Bronze
- Connector: 50μ" of Selective Gold Contact Plating
 - Area, Gold flash over the remainder
 - Over 2.54μm[.000100] thick nickel underplate
- Conductor(X6C): 26AWG (0.12X12) Bare Copper
- Insulation(X6C): PP6331 ID 0.95-1.0
- Jack: PVC No UL 80 P
- Package: Individual PE Bag

SEC: A-A

[illegible]

Item No.	
----------	--

AT-C-26-6/6/B-5/R

	Title
--	-------

NON-UL 26 AWG (0.12X12)*6C, O.D.: 2.4*6.8MM,
Standard Plug, 50μ" of contact plating, BLACK

Drawing No.

rev00

Replace

Sheet

