

Product data sheet

Specifications



APC 150kVA Modular PDU Bottom Feed Side Car, 300mm

PDPM150SC

Overview

Lead time	Usually Ships within 3 Weeks
-----------	------------------------------

Main

Main Input Voltage	208 V 208 V 3 phases 480 V 3 phases 600 V 3 phases
Main Output Voltage	208 V 208 V 3 phases 415 V 3 phases 480 V 3 phases 600 V 3 phases
Provided equipment	Installation guide

Physical

Colour	Black
Height	200.4 cm
Width	30 cm
Depth	107 cm
Net weight	134 kg
Mounting preference	No preference
Mounting mode	Not rack-mountable

Input

Network frequency	60 Hz
Number of input connectors	1 hard wire 5 wire (3P + N + E)
Input current limits	200 A

Output

Max current draw	200 A
------------------	-------

Conformance

Standards	UL 60950-1
-----------	------------

Environmental

Ambient air temperature for operation	-5...40 °C
---------------------------------------	------------

Relative humidity	0...95 %
Operating altitude	0...10000 ft
Ambient air temperature for storage	-25...65 °C
Storage Relative Humidity	0...95 %
Storage altitude	0...3048 m

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	215 cm
Package 1 Width	121 cm
Package 1 Length	84.8 cm
Package 1 Weight	155 kg
SCC14	10731304296253

Contractual warranty

Warranty	1 year repair or replace
----------	--------------------------



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

Materials and Substances

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Under investigation

Use Again

Repack and remanufacture

Take-back	No
-----------	----

Image of product / Alternate images

Alternative

