

## Han HPR SP1-HTE-SCL-M25



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 011 0411
Specification	Han HPR SP1-HTE-SCL-M25
HARTING eCatalogue	<a href="https://harting.com/19400110411">https://harting.com/19400110411</a>

### Identification

Category	Hoods / Housings
Series of hoods/housings	Han® HPR
Type of hood/housing	Hood

### Version

Size	SP1
Version	Top entry
Number of cable entries	1
Cable entry	1x M25
Locking type	Screw locking
Field of application	Hoods/housings for harsh outdoor environments

### Technical characteristics

Tightening torque	6 Nm Locking screw
	6 Nm Fixing screws
	10 Nm Retaining ring
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65
	IP68
	IP69 / IPX9K acc. to ISO 20653
Type rating acc. to UL 50 / UL 50E	4
	4X
	12



**Pushing Performance**  
Since 1945

## Material properties

Material (hood/housing)	Aluminium die-cast Corrosion resistant
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	CE DNV GL

## Commercial data

Packaging size	1
Net weight	253 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140831735
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466