

Data Sheet | Item Number: 247-508
Mini-WSB marking card; as card; MARKED; 24 V (100x); not stretchable; Horizontal marking; snap-on type; white
<https://www.wago.com/247-508>



Color: white Similar to illustration

Technical data		
Suitable		for WAGO I/O System
Marking method		Thermal transfer
Marking		24 V
Marking (number)		100
Marking direction		Horizontal marking
Marking color		black
Marking type		Symbol
Marking layout		Same symbols per strip
Delivery form		Marker card
Delivery form configuration		10 strips with 10 markers per card

Physical data	
Height	152 mm / 5.984 inches
Width	56.8 mm / 2.236 inches
Depth	3.2 mm / 0.126 inches
Marker/strip width	5 mm
Marker width	5 mm

Mechanical data	
Smear resistance	EN 60998-1:2004

Material data	
Color	white
UV resistance	EN 60068-2-5:2010 Procedure B
Halogen-free	Yes
Weight	6.2 g
Fire load	0.185 MJ



Commercial data	
Product Group	2 (Terminal Block Accessories)
PU (SPU)	50 (5) pcs
Packaging type	Box
Country of origin	DE
GTIN	4017332253345
Customs tariff number	49119900000

Product Classification	
UNSPSC	55121718
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 8.0	EC000761
ECCN	NO US CLASSIFICATION

Environmental Product Compliance	
RoHS Compliance Status	Compliant,No Exemption

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 247-508

↓

Installation Notes

Marking



Marking via Mini-WSB Quick Marking System.