

 Live Product Chat US Only
8:30am - 5pm ET, Mon - Fri



Product Highlights:

- [View all Features](#) | [Find Similar Products](#)

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)

Product Drawings:

- [TAB, FASTON, 4.75 \[.187\] SERIES](#) (PDF, English)

Catalog Pages/Data Sheets:

- ? None Available

Product Specifications:

- ? None Available

Application Specifications:

- [FASTON Straight Receptacles with "F" Crimp Feature \(PDF, English\)](#)

Instruction Sheets:

- ? None Available

CAD Files: ([CAD Format & Compression Information](#))

- ? 2D Drawing (DXF, Version A)
- ? 3D Model (IGES, Version A)
- ? 3D Model (STEP, Version A)

List all Documents

Additional Information:

- ## ? Product Line Information

Related Products:

- ## ? Tooling

Product Type Features:

- ? Product Type = Tab
 ? Insulation = No
 ? Tab Fit (mm [in]) = 4.75×0.81 [.187 x .032]
 ? Material = Brass
 ? Finish = Tin
 ? Wire/Cable Type = Regular Wire
 ? Mount Angle = Straight
 ? Insulation Support = Without
 ? CSA Certified = Yes
 ? Comment = Premilled dual stock thickness.

Body Related Features:

- ? Tab Type = Wire Crimp
 ? Wire Range (mm [AWG]) = 0.80 -2.00 2 [18-14]
 ? Stud Hole = Without
 ? UL Rating = Listed

Industry Standards:

- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

Packaging Related Features:

- ? Packaging Method = Strip

Other:

- ? Brand = AMP