Power Cord, C19 to NEMA L6-20 - Heavy-Duty, 20A, 250V, 12 AWG, 14 ft. (4.27 m), Black

MODEL NUMBER: **P040-014**






Heavy-duty power cord supplies power to network devices that require a heavy-gauge connection, such as larger servers and switches.

Features

C19 to L6-20P Power Cable for Network Devices That Require a Heavy-Gauge Connection This 12 AWG power cable is designed for servers, routers, network switches, blade server enclosures and other devices that require a heavy-gauge connection capable of managing high power levels. The fully molded C19 end connects to your device's C20 inlet, and the fully molded NEMA L6-20P plug connects to an AC power source up to 14-ft. (4.27 m) away. The 14-ft. (4.27 m) length allows you great flexibility in placing equipment with respect to the power outlet.

Locking Connector Helps Prevent Accidental Disconnection and Expensive Downtime Having a cable come loose accidentally can mean the loss of power and costly downtime. The locking NEMA L6-20P connector helps you avoid such danger, protecting critical equipment by maintaining a secure link without failure. The locking connector is also invaluable when moving equipment in a rack or removing equipment from tight areas, ensuring the heavy-duty power cable always stays connected.

Highlights

- Recommended for powering servers, switches and other essential network devices
- L-60 locking connector maintains secure link to avoid loss of power and costly downtime
- Thick 12 AWG wire gauge manages high power levels required for larger equipment
- C19 to L6-20P power cord is ideal replacement for worn-out or missing cable
- Extra-long 14-ft. (4.27 m) cord provides flexibility in placing connected device away from outlet

Applications

- Connect network devices like servers, switches and blade server enclosures to a PDU up to 14-ft. (4.27 m) away in your data center
- Extend an existing power connection up to 14-ft. (4.27 m) to more easily place a device or reach a power source in a rack
- Replace a worn-out or missing heavy-gauge power cord

Package Includes

- P040-014 C19 to L6-20P Power Cord, 14-ft. (4.27 m), Black

Specifications

OVERVIEW	
UPC Code	037332164933
Product Type	PDU Extension Power Cord
Device Compatibility	Server; Router; Network Switch; UPS; PDU
Country/Region	North America
INPUT	
Maximum Input Amps	20
Voltage Compatibility (VAC)	250

Downloaded from Arrow.com.

CONNECTIONS	
Side A - Connector 1	NEMA L6-20P
Side B - Connector 1	IEC-320-C19
Connector Style	Straight
PHYSICAL	
Color	Black
Plug Color	Black
Cable Jacket Color	Black
Connector Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	FT2
Power Cord Jacket Type	SJT
Cable Outer Diameter (OD)	11mm
Number of Conductors	3
Wire Gauge (AWG)	12
Wire Gauge (OD - mm^2)	3.31
Power Cord Color	Black
Cable Length (ft.)	14
Cable Length (m)	4.27
Shipping Dimensions (hwd / in.)	12.00 x 10.00 x 0.50
Shipping Dimensions (hwd / cm)	30.48 x 25.40 x 1.27
Shipping Weight (lbs.)	2.40
Shipping Weight (kg)	1.09
Unit Dimensions (hwd / in.)	12.000 x 10.000 x 0.500
Unit Weight (lbs.)	2.4
Unit Weight (kg)	1.09
ENVIRONMENTAL	
Operating Temperature Range	-4° to 194°F (-20° to 90°C)
Storage Temperature Range	-4° to 194°F (-20° to 90°C)
Operating Humidity Range	20% to 70% RH
Storage Humidity Range	20% to 80% RH
FEATURES & SPECIFICATIONS	
Antibacterial	No

Downloaded from Arrow.com.

Angled Plug	No
High Voltage	Yes
Locking Plug	Yes
Coiled Power Cord	No
Locking Power Cord	Yes
Locking	Yes
STANDARDS & COMPLIANCE	
Product Certifications	cUL Listed; UL Listed
Product Compliance	RoHS
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	Lifetime limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
https://tripplite.eaton.com

© 2026 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.

Downloaded from Arrow.com.