

Product Line

Single Pair Ethernet >

ZConnect >

Ceres >

Accessory

Large Size

Macro Size

Middle Size

Mini Size

Others (GBD)

Others (MAB)

Others (PLD)

Standard Size

X-Lok >

M Series >

FLOS & FLOS+ >

Power >

RBL >

HS-Lok >

NMEA 8888 >

ABOUT AMPHENOL LTW

Heavy Duty Shielded >

RJ >

USB >

SSL >

HDMI >

DVI >

Fiber Optic >

RF >

Cable Joiner >

Cable Gland >

Pressure Relief Vent >

LED Light Guide >

D-Sub >



DCD-12PMDP-LC7001

Operating Temperature: -40°C ~ +105°C

Transmission Speed: N/A

Shielded: Plastic, Non-shielded

Jacket Material: N/A

Certificate: N/A

You must login first for view the price

Quantity

- 1 +

Add to Cart

Inquiry



Can't find? [Customize your part](#)

Mating Pair & Accessories

Connector Type

Search



Ceres, Accessory, Dust..
CAP-DADMDPC1
-40°C ~ +105°C



Ceres, Accessory,...
CAP-WADMLMA1
-40°C ~ +105°C



Ceres, Accessory,...
CAP-WADMLPB1
-40°C ~ +105°C



Ceres, Accessory,...
CAP-WADMLPB2
-40°C ~ +105°C

Add to Cart

Inquiry

Specifications

Download / CAD

Nominal Current

20A+5A

Connector Type

Receptacle

Shielded

Plastic, Non-shielded

No. of Contacts

12

Connector Gender

Male

Backshell

Circular

Mating Style

2 Points Lock

IP Rating

IPX7

Assembly Style

PCB 180°

More Options

People Also Bought

