



Part Number : [2032630001](#)
Product Description : Sentrality 8.00mm Knurled Press-fit Pin, 26.00mm Engagement Length, Bag
Series Number : 203263
Status : Active
Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[2032630001_sd.pdf](#)
[2032630006-PK-000.pdf](#)

3D Models and Design Files

[STEP AP242](#)
[SOLIDWORKS](#)
[Creo](#)
[Symbol and Footprint \(Multi-Format\)](#)

Specifications

[2043130001-AS-000.pdf](#)
[2043130001-PS-000.pdf](#)
[2043130008-TS-000.pdf](#)
[2043131234-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	203263
Description	Sentrality 8.00mm Knurled Press-fit Pin, 26.00mm Engagement Length, Bag
Application	Board-to-Board, Busbar-to-Board, Busbar-to-Busbar, Power
Component Type	PCB Header
Product Name	Sentrality
UPC	191128426985

Electrical

Current - Maximum per Contact	200.0A
Voltage - Maximum	600V

Physical

Breakaway	No
Circuits (Loaded)	1
Circuits (maximum)	1

Diameter	8.00mm
Durability (mating cycles max)	200
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	No
Height Above Board	26.00mm
Material - Metal	Copper Alloy
Material - Plating Mating	Silver
Material - Plating Termination	Silver
Net Weight	13.087/g
Number of Rows	1
Orientation	Vertical
Packaging Type	Bag
PCB Retention	None
Pitch - Mating Interface	N/A
Polarized to Mating Part	No
Polarized to PCB	No
Temperature Range - Operating	-40° to +125°C
Termination Interface Style	Press-Fit

Mates With / Use With

Mates with Part(s)

Description	Part Number
Sentrality Top-entry Surface Mount Socket Assemblies	<u>204318</u>
Sentrality Top-entry Surface Mount Socket Assemblies with Self-alignment Capability	<u>204365</u>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies with Self-alignment Capability	<u>204313</u>
Sentrality Top-entry Knurled Press-Fit Socket Assemblies	<u>204316</u>
Sentrality 3.40mm Right-Angle Socket Assemblies	<u>205000</u>

This document was generated on Oct 17, 2025