Part Number : 2244162116
Product Description : SW1-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 11.00mm Diameter, Female, 1000.00mm Length, 4/0 AWG, Black
Series Number : 224416
Status : Active
Product Category : Power and Signal Cable Assemblies



Documents and Resources

Drawings

2244162116_sd.pdf

Specifications

2244100011-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power and Signal Cable Assemblies
Series	224416
Description	SW1-to-Pigtail Off-the-Shelf (OTS) Cable Assembly, 11.00mm Diameter, Female, 1000.00mm Length, 4/0 AWG, Black
Application	Wire-to-Busbar, Wire-to-Board
Assembly Configuration	Single Ended Connector
Connector to Connector	SW1 11.00mm-to-Pigtail
Product Name	SW1
Type	Discrete Wire Assembly
UPC	196823528736

Electrical

Current - Maximum per Contact	300.0A
Voltage - Maximum	1000V

Physical

Cable Length	1000.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Black
Gender	Female-Pigtail
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Silver

Downloaded from Arrow.com.

Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	1410.876/g
Number of Rows	1
Overmolded	No
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1015
Wire Size (AWG)	4/0

Mates With / Use With

Mates with Part(s)

Description	Part Number
SW1 11.00mm Knurled Press-fit Locking Pins	218336

Downloaded from Arrow.com.