

 PRODUCTS ▾

 DISTRIBUTOR INVENTORY

 INDUSTRIES ▾

 SUPPORT ▾

 NEWS & EVENTS ▾

 ABOUT US ▾

64AT22-5


Products > Switches > Toggle Switches > AT Series > **64AT22-5**

Overview

MICRO SWITCH AT Series Toggle Switch, 4 pole, 3 position, Quick Connect terminal, Standard Lever.

MICRO SWITCH AT toggle switches provide a compact

[View More](#)



 view all 64AT22-5 literature

 view distributor inventory

 sample request

 email support

 get support

 email sales

 find a distributor

 email this page

Technical Specifications

Product Type	MICRO SWITCH Toggle	Ampere/Voltage Range (Resistive Load)	0.1 A to 7.0 A at 0.5 Vdc to 28 Vdc
Circuitry	4PDT	Action	3 position
Circuitry/Operating action	Keyway Position Pole 1&2 C-NC Pole 3&4 C-NO	Center Position C-NC	Opposite Position C-NO C-NC
Termination	Quick Connect	Mounting	Bushing 15/32 in
Availability	Global	Comment	FAA-PMA approved
		UNSPSC Code	39122211

[View More](#)

View documents in: English ▾

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
 AT Series Toggle Switch Assemblies	Catalog Information	English	427KB
 Sensors and Switches in Oil Rig Applications	Application Note	English	7MB
 Flight Deck Toggle Switches	Application Note	English	185KB
 Oil and Gas Brochure	Brochure	English	4MB

[View More](#)

Product Features

- Gold or silver contacts
- Choice of sealed bushing
- Standard or pull to unlock toggle lever
- Short behind-panel depth
- Solder or quick connect termination
- 2,4,6, or 8 SPDT precision basic switches
- 2 or 3 position, momentary or maintained action

Applications

- Industrial machinery and equipment
- Military and commercial aviation
- Construction equipment
- Test instruments

- Agricultural machinery
- Process control
- Medical instrumentation

NAVIGATION LINKS

- HOME PAGE
- PRODUCTS
- DISTRIBUTOR INVENTORY
- INDUSTRIES
- SUPPORT
- NEWS & EVENTS
- ABOUT US

DISTRIBUTOR LINKS

- ECOM LOGIN
- LEARN CENTER
- REQUEST ACCESS TO ECOM
- SALES/AD PORTAL LOGIN
- SALES/AD PORTAL ACCESS REQUEST
- SAMPLE REQUEST
- SUPPLIER MICROSITE

LANGUAGE

English 

SOCIAL MEDIA**SITE INFORMATION**

PRIVACY STATEMENT

SITEMAP

TERMS & CONDITIONS

COPYRIGHT © 2018 HONEYWELL
INTERNATIONAL INC.