



Part Number : [1301350296](#)
Product Description : Super-Safeway Angled Outlet Box, F3 (3/4") Cord Grip Body, Including (2) NEMA 5-20 Duplex Receptacles with Flip Lids & Plug, 15.24m (50.0') Cord Length, 12/3 SOW Cord
Series Number : 130135
Status : Active
Product Category : Power Distribution
Engineering Number : 3332RB123



Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Relevant

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Power Distribution
Series	130135
Description	Super-Safeway Angled Outlet Box, F3 (3/4") Cord Grip Body, Including (2) NEMA 5-20 Duplex Receptacles with Flip Lids & Plug, 15.24m (50.0') Cord Length, 12/3 SOW Cord
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Type	Angled Outlet Box
UPC	78678828895

Electrical

Current - Maximum per Contact	20.0A
GFCI	No
GFCI Reset	N/A
Ground Continuity Monitor	No
Open Neutral Relay	N/A
Voltage - Maximum	125V

Physical

Cord Diameter	15.24mm (.600")
Cord Grip Body Size	F3 3/4"
Cord Length	15.24m (50.0')
Cord Type	12/3 SOW
Feed-Thru	No
Flip Lid	Yes
Material - Housing	Rubber
Mounting Style	Portable

Number of Receptacles	2
Packaging Type	Carton
Receptacle Type	Duplex

This document was generated on Sep 23, 2025