Product Line

- DeepTronica
- Single Pair Ethernet
- ZConnect
- Ceres
- X-Lok
- M Series
  - Accessory
  - M5
  - Guided M8
  - M8
  - M10.5
  - M12 (A)
  - M12 (B)
  - M12 (D)
  - M12 (I)
  - M12 (K)
  - M12 (L)
  - M12 (S)
  - M12 (T)
  - M12 (X)
  - M23
- FLOS & FLOS+
- Power
- RBL
- HS-Lok
- NMEA 2000
- Heavy Duty Shielded
- RJ
- USB
- SSL
- HDMI
- DVI
- Fiber Optic
- RF
- Cable Joiner
- Cable Gland
- Pressure Relief Vent
- LED Light Guide
- D-Sub







MSAS-05PFFT-EE0001

- Operating Temperature: -55°C ~ +125°C
- Transmission Speed: N/A
- Shielded: Plastic, Shielded
- Jacket Material: N/A
- Certificate: UL2238

You must login first for view the price

Quantity − 1 +

Check Stock

Add to Cart | Inquiry

Can't find? Customize your part

Mating Pair & Accessories

Connector Type

Search



M Series,...
APPM-AAAFA012-...
N/A
− 0 +



M Series,...
APPM-AAAFA012-...
N/A
− 0 +



M Series,...
APTM-BMZFA012-...
N/A
− 0 +



M Series,...
APTM-BMZFA012-...
N/A
− 0 +



M Series,...
CAP-WBDFSMA1
-40°C ~ +105°C
− 0 +



M Series,...
CAP-WBDFSMA2
-40°C ~ +105°C
− 0 +

Add to Cart | Inquiry

Specifications | Download / CAD

Nominal Current **4A**	Connector Type **SMT**
Shielded **Plastic, Shielded**	No. of Contacts **05**
Connector Gender **Female**	Backshell **N/A**
Mating Style **N/A**	IP Rating **Non-waterproof**
Assembly Style **SMT 180°**	

More Options

People Also Bought



MSAS-05PFFT-...



AB-DC02FR-DCFR-...



M12A06ML-12AMR-...



BD-07AFFM-SL6A02



AB-CD09ML-CDFR-...

Downloaded from Arrow.com.