Part Number : 1301530147
Product Description : Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA L6-20, 20A, 240V, 1.83m (6.0') Cord Length
Series Number : 130153
Status : Active
Product Category : Power Distribution
Engineering Part Number : 20054-6



Documents and Resources

Drawings

1301530147_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Power Distribution
Series	130153
Description	Safeway In-Line Commercial GFCI, Permanent Mount, Single Phase, Manual Reset, NEMA L6-20, 20A, 240V, 1.83m (6.0') Cord Length
Enclosure Rating	NEMA 4
NEMA Configuration	NEMA L6-20
Product Name	Safeway
Type	GFCI Commercial Duty, Single Phase
UPC	78678837417

Agency

CSA	LR6837
UL	E66308

Electrical

Current - Maximum per Contact	20.0A
GFCI	Yes-In-line
GFCI Reset	Manual
Ground Continuity Monitor	No
Open Neutral Relay	Yes
Voltage - Maximum	240V

Physical

Cord Diameter	10.92mm (.430")
Cord Grip Body Size	Internal Double C-Clamp
Cord Length	1.83m (6.0')
Cord Type	12/3 SJTW
Feed-Thru	Yes

Downloaded from Arrow.com.

Flip Lid	No
Material - Housing	Nylon
Mounting Style	Portable
Number of Receptacles	1
Packaging Type	Bag
Receptacle Type	N/A

Downloaded from Arrow.com.