



Part Number : 1122191018

Series Number : 112219

Product Category : Wiring Devices

Product Description : Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7, Three Grommets Included

Status : Active

Engineering Number : ARC30MHDAB04


Documents & Resources

Drawings

Drawing 1122191018_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2023)8585-DC (23 Jan 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Wiring Devices
Series	112219
Description	Woodhead ArcArrest Plug with Handle, Drawplates, and Cap, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7, Three Grommets Included
IP Rating	IP69K
NEMA Configuration	N/A
Product Family	Woodhead ArcArrest Connector System
Product Name	ArcArrest
Specialty	Switch-Rated
Type	Plug
UPC	78172558538

Agency

UL	E145922
----	---------

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	125V / 250V AC

Physical

Cord Grip Body Size	F4 1"
Cord Type	N/A
Flange	Yes
Flip Lid	No
Gender	Male
Length	178.99mm (7.047")
Lighted Connector	No
Locking Blade	N/A
Net Weight	1.000/g

Poles	2
Receptacle Type	N/A
Wire Size (AWG)	8 to 12

Mates With / Use With

Mates with Part(s)

Description	Part Number
Woodhead ArcArrest Receptacle, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7	<u>1122190004</u>
Woodhead ArcArrest Receptacle with Handle and Drawplates, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7, Three Grommets Included	<u>1122190018</u>
Woodhead ArcArrest Receptacle with Handle, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7, Three Grommets Included	<u>1122190032</u>
Woodhead ArcArrest 70° Angle Receptacle, Switch-Rated, 30.0A, 125/250V AC, 2-Pole+Neutral+Ground, Insulator Keying Position 7	<u>1122190046</u>

This document was generated on Jul 21, 2024