

Data Sheet | Item Number: 249-247

WCB marker tag; MARKED; 7. (20x); not stretchable; Horizontal marking; snap-on type; white

<https://www.wago.com/249-247>



Color: white

Similar to illustration

Technical data

Marking method	Thermal transfer
Marking	7.
Marking (number)	20
Marking direction	Horizontal marking
Marking color	black
Marking type	Numbers
Delivery form	Marker card
Flammability class per UL94	V2

Physical data

Height	3.6 mm / 0.142 inches
Width	2.6 mm / 0.102 inches
Depth	118.2 mm / 4.654 inches

Mechanical data

Smear resistance	EN 60998-1:2004
------------------	-----------------

Material data

Color	white
Halogen-free	Yes
Weight	0.5 g
Fire load	0.014 MJ

UNSPSC	55121612
eCl@ss 10.0	27-14-11-37
eCl@ss 9.0	27-14-11-37
ETIM 9.0	EC000761
ETIM 10.0	EC000761
ECCN	NO US CLASSIFICATION

RoHS Compliance Status	Compliant, No Exemption
------------------------	-------------------------

Environmental Product Compliance

Environmental Product Compliance 249-247