
Part Number : 191930198
Product Description : VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 6 (M3.5), Carton
Series Number : 19193
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : D-356-06



Documents and Resources

Drawings

191930198_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-013-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19193
Description	VersaKrimp Ring Tongue Terminal for 8 AWG Wire, Closed-Brazed Barrel, Stud Size 6 (M3.5), Carton
Keyword	Ring Terminal, Ring Terminals
Product Name	VersaKrimp
Style	Ring
Type	Ring Terminal, Metric Ring Terminal
UPC	800755050530

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Net Weight	2.972/g
Packaging Type	Carton
Stud Size	6 (M3.5)

Downloaded from Arrow.com.

Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	7.19mm max.
Wire Size (AWG)	8
Wire Size mm^2	8.36

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	192860117
Die Set (Large) for the HHLS Hydraulic Crimper	192900001
PremiumGrade Hand Crimp Tool for 8-2 AWG Terminals	640013900
RHT1080 Hand Crimp Tool	640034400
Square “DIN” style dies for 8 AWG	640037670
Crimp Head for the AT-200 Pneumatic Hand Tool	640074400
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	638162000

Downloaded from Arrow.com.