Part Number : 135120001
Product Description : Button RFID Tag, 20.1mm Read Range, 10.00mm Diameter Footprint, For Metal Surfaces, Adhesive Attachment
Series Number : 13512
Status : Active
Product Category : Asset Tracking



Documents and Resources

Drawings

135120001_sd.pdf

Specifications

135120001-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Reviewed
China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Downloaded from Arrow.com.

Additional Product Compliance Information

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Asset Tracking
Series	13512
Description	Button RFID Tag, 20.1mm Read Range, 10.00mm Diameter Footprint, For Metal Surfaces, Adhesive Attachment
Component Type	RFID Tag
Product Name	RFID Solutions
Type	For Metal Surfaces
UPC	196823153303

Electrical

Frequency	13.56 MHz

Physical

Dimensions	10.00mm dia x 2.60mm Thickness
Mounting Style	Adhesive
Net Weight	1.400/g
Outer Diameter	10.00mm
Packaging Type	Bag
Read Range	20.1mm
Thickness	2.60mm

Downloaded from Arrow.com.