Part Number : 5055650701
Product Description : 1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 7 Circuits, Black
Series Number : 505565
Status : Active
Product Category : Connector Housings



Documents and Resources

Drawings

5055650701_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

5055650701.dxf

Specifications

5055650000-AS-000.pdf

5055659200-200.pdf

5055650000-000.pdf

5055650003-PS-000.pdf

5055651000-PS-000.pdf

5055650002-000.pdf

5055651002-PS-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC

Downloaded from Arrow.com.

	61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Connector Housings
Series	505565
Description	1.25mm Pitch, Micro-Lock Plus Receptacle Crimp Housing, Single Row, Positive Lock, 7 Circuits, Black
Application	Signal, Wire-to-Board, Wire-to-Wire
Keyword	Micro-Lock Plus 1.25
Product Name	Micro-Lock Plus
UPC	889056502924

Agency

UL	E29179

Downloaded from Arrow.com.

Physical

Circuits (maximum)	7
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	No
Lock to Mating Part	Yes
Material - Resin	Polybutylene Terephthalate (PBT)
Net Weight	149.585/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Pitch - Termination Interface	1.25mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C

Mates With / Use With

Mates with Part(s)

Description	Part Number
1.25mm Pitch Micro-Lock Plus Vertical, Single Row, Surface Mount Headers	505568
1.25mm Pitch Micro-Lock Plus Right-Angle, Single Row, Surface Mount Headers	505567

Use with Part(s)

Description	Part Number
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, Matte Tin (Sn) Plating, 150.00mm Length, 26 AWG, Black	797581148
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock	797581149

Downloaded from Arrow.com.

Plus 1.25 Female, Matte Tin (Sn) Plating, 300.00mm Length, 26 AWG, Black	
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, 0.10µm Gold (Au) Plating, 150.00mm Length, 26 AWG, Black	797582143
Pre-Crimped Lead Micro-Lock Plus 1.25 Female-to-Micro-Lock Plus 1.25 Female, 0.10µm Gold (Au) Plating, 300.00mm Length, 26 AWG, Black	797582144
1.25mm Pitch Micro-Lock Plus Female Crimp Terminals	505431

Downloaded from Arrow.com.