

Product data sheet

Specifications



APC Replacement battery cartridge #153 with 2 Year Warranty

APCRBC153

Overview

Lead time	Usually in Stock
-----------	------------------

Main

Battery type	Lead-acid battery
Provided equipment	All required connectors Installation guide

Physical

Colour	Black
Height	5.1 cm
Width	9.83 cm
Depth	15.1 cm
Net weight	1.53 kg
Mounting mode	Not rack-mountable

Output

Battery capacity	4200 mA.h
------------------	-----------

Environmental

Ambient air temperature for operation	0...40 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	0...40 °C
Storage altitude	0.00...3048.00 m
Storage Relative Humidity	0...95 %

Batteries & Runtime

Number of battery free slots	0
Number of battery filled slots	0
Device mounting	Enclosed battery cartridge

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Battery voltage	12 V
Number of battery replacement quantity	1

Packing Units

Package 1 Weight	1.8 kg
Package 1 Height	8.9 cm
Package 1 width	17.5 cm
Package 1 Length	21.3 cm
SCC14	10731304314186
Number of Units in Package 3	240

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace
----------	---------------------------