




PC-Board layout
view component side
thickness 1,6

Connector insertion force on PCB = max. 80N

09683537611	M3	PL3
09683535611	M3	PLS4
09683537612	4-40 UNC	PL3
09683535612	4-40 UNC	PLS4
Part number	Nut thread	Performance level

		All Dimensions in mm Original Size DIN A4		Scale 1:1		Free size tol.		Ref.					
		All rights reserved		Created by ZENGD		Inspected by LUOK		Standardisation HOFFMANN					
		Department EC PD - CN		Date 2017-11-07		State Final Release		Sub.					
		HARTING Electronics GmbH		Title D-Sub STD 25-pole female angled board locks						Doc-Key / ECM-Nr. 100539805/UGD/001/C 500000126855			
D-32339 Espelkamp				Type TB		Number 0968353X61X				Rev. C		Page 1/1	