








Verpackt im Gurt in Anlehnung an DIN IEC 60286-3
tape on reel packaging according to DIN IEC 60286-3
Verpackungseinheit: 800 Stück
packaging unit: 800 pcs






Abspulrichtung - *reel off direction*



Leiterplatten-Layout Vorschlag
PCB-Layout Proposal



Koplanarität der Anschlüsse ≤ 01 mm
coplanarity area of termination ≤ 0,1 mm

RoHS: 6/6
MSL: 1

zweireihig, mit Zapfen
2 row, with pegs

Dimension no.	Tolerances ISO 8015	All Dimensions in mm	Scale 5:1 / Material

Customer drawing:
This Drawing is a controlled Document.

Subject to modification without prior notice.
Drawing will not be updated.

MicroStac Steckverb., 54 polig
MicroStac Conn., 54 contacts

TE Connectivity

C-354000-E

C

A3

Index		Date	
j1		15.05.2023	

Class MICROS

Die deutsche Version dieser Zeichnung dient nur zur Erleichterung der Handhabung. Bei Abweichungen von dem englischen Original gilt das englische Original.
The german version of this drawing has been offered for convenience only and may deviate from the english original. In case of any deviation the English version shall prevail.

Weitergabe sowie Vervielfältigung dieses Dokuments, Verwertung und Mitteilung seines Inhalts sind verboten, soweit nicht ausdrücklich gestattet. Zuwiderhandlungen verpflichten zu Schadenersatz. Alle Rechte für den Fall der Patent-, Gebrauchsmuster- oder Geschmacksmustereintragung vorbehalten.
The reproduction, distribution and utilization of this document as well as the communication of its contents to others without express authorization is prohibited. Offenders will be held liable for the payment of damages. All rights reserved in the event of the grant of a patent, utility model or design.

Downloaded from Arrow.com.