




REVISIONS				
ZONE	LTR	ECN	DESCRIPTION	DATE
	D	23231	REVISED & REDRAWN.	7/5/78
	E	23735	UPDATED REV. LETTER 44	10/19/78
	F	28523	.050 MAX. WAS: .044 MAX.	2-28-84


NOTES :

1. CABLE ACCEPTANCE DIMENSIONS : CENTER CONDUCTOR .013 MAX , DIELECTRIC .036-.032 SHIELD .054-.048, JACKET .087-.065 .
2. FOR ASSEMBLY INSTRUCTIONS , REFER TO CI-ASMB-1.
3. TEFLON PER L-P-403 .
4. BERYLLIUM COPPER PER QQ-C-530, HALF HARD
5. BRASS PER QQ-B-626, COMP 360, HALF HARD.
6. GOLD PLATE PER MIL-G-45204 , TYPE II , CLASS 1, GRADE C .
7. SILVER PLATE PER QQ-S-365 TYPE II , CLASS 3, GRADE B .
8. THIS CONTACT IS UTILIZED ON THE CIRCULAR CONNECTORS , SEE MALCO'S CATALOG 200-2 .

Tyco Dwg 5-1532129-7
Micro P/N 084-0024-00T2

QTY.	PT. NO.	DESCRIPTION	ITEM NO.
PARTS LIST			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES $\pm \frac{1}{64}$.XX $\pm .03 \pm 3^\circ$.XXX $\pm .015$			
CONTRACT NO.		MALCO A MICRODOT COMPANY, INC. 220 PASADENA AVE., SO. PASADENA, CALIF. 91030	
APPROVALS		DATE	PROD. CODE
DRAWN E. MINGURA		4-7-78	984
CHECKED		4-7-78	CODE
PR. ENG. PC		7/5/78	CD
APPROVED			
MATERIAL		SIZE	CODE IDENT NO.
3 4 5		B	98278
FINISH		DRAWING NO.	
6 7		084-0024-00T2	
NEXT ASSY		SCALE	SHEET 1 OF 1
USED ON			
APPLICATION			
DO NOT SCALE DRAWING			

REVISIONS					
ZONE	LTR	ENC	DESCRIPTION	DATE	APPROVED
	D	23231	REVISED & REDRAWN.	7/5/78	REC
	E	23735	UPDATED REV. LETTER QW	10/19/78	RE
	F	28523	.050 WAS: .044 .030 .030	7/28/87	RMJ



NOTES :

- 1 CABLE ACCEPTANCE DIMENSIONS : CENTER CONDUCTOR .013 MAX, DIELECTRIC .036-.032, SHIELD .054-.048, JACKET .087-.065.
- 2. FOR ASSEMBLY INSTRUCTIONS, REFER TO CI-ASMB-1.
- 3 FOR COMPONENT FINISH, REFER TO MEP 202-08.

	1	083-0561-00R4	COAXIAL SOCKET CONTACT	5
	1	083-0001-00Q6	RING, JERK	4
	1	083-0002-0000	BUSHING, BACK-UP	3
	1	083-0549-0000	BUSHING, PLUG	2
	1	083-0555-00Q6	HOUSING, PLUG	1
	QTY.	PT. NO.	DESCRIPTION	ITEM NO.

PARTS LIST

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES $\pm \frac{1}{64}$.XX $\pm .02 \pm 3^\circ$.XXX $\pm .010$		CONTRACT NO.		MALCO A MICRODOT COMPANY, INC. 220 PASADENA AVE., SO. PASADENA, CALIF. 91030			
		APPROVALS					
		DATE					
		DRAWN E. MINGURA 4-7-78					
MATERIAL		CHECKED	4-12-78	CONTACT PIN COAXIAL ASSY (50 OHM) INTER-CHANGEABLE COAX. CONTACT		PROD. CODE 984 CODE M	
FINISH		PR. ENG. REC	7/5/78				
APPROVED							
NEXT ASSY		USED ON		SIZE B		CODE IDENT NO. 98278	DRAWING NO. 084-0024-00T2
APPLICATION		DO NOT SCALE DRAWING		SCALE		SHEET 1 OF 1	