



**Part Number :** [1301030050](#)

**Product Description :** Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Grounded Insulated Reflector Guard, Cord Type 16/3 SOOW, 7.62m (25.0') Cord Length

**Series Number :** 130103

**Status :** New Business Not Supported

**Product Category :** Lamps and Lights

**Engineering Number :** 1203RIA163



---

## Documents & Resources

---

### Product Environment Compliance

#### Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

#### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

### Part Details

#### General

Status	New Business Not Supported
Category	Lamps and Lights
Series	130103
Description	Watertite Wet Location Incandescent Hand Lamp, 100W with Screw Release Grounded Insulated Reflector Guard, Cord Type 16/3 SOOW, 7.62m (25.0') Cord Length
NEMA Configuration	NEMA 5-15
NEMA Rating	NEMA 4X
Product Family	Hand Lamps
Product Name	Watertite
Type	Hand Lamps
UPC	78678861357

#### Agency

CSA	LR85374
-----	---------

#### Electrical

Lamp Wattage - Maximum	100W
Lumens	1000
On/Off Switch	No
Voltage (Fixture) - Maximum	120V AC

#### Physical

Bulb Type	Incandescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	N/A
Cord Type - Primary	16/3 SOOW
Depth	120.65mm (4.750")
Duty	Wet Location
Guard Included	Yes
Guard Type	Grounded, Insulated, Reflector, Screw Release
Height	457.20mm (18.000")
Lamp Type	A21

Length	N/A
Material - Globe	Tempered Glass
Material - Guard	#8 Gauge Zinc-plated Steel
Mounting Style	Hand Held
Outlet	None
Packaging Type	Carton

---

This document was generated on Dec 30, 2023

---