

|                              |                          |                      |
|------------------------------|--------------------------|----------------------|
| THIS DRAWING IS UNPUBLISHED. | RELEASED FOR PUBLICATION | 20                   |
| © COPYRIGHT 20               | BY -                     | ALL RIGHTS RESERVED. |


| REVISIONS |     |               |           |     |      |
|-----------|-----|---------------|-----------|-----|------|
| P         | LTR | DESCRIPTION   | DATE      | DWN | APVD |
|           | C1  | ECR-19-013004 | 23AUG2019 | SR  | JL   |
|           | C2  | ECR-19-014098 | 12SEP2019 | SR  | JL   |
|           | C3  | ECR-20-000836 | 23JAN2020 | SB  | JL   |
|           | D   | ECR-22-151735 | 07MAR2023 | RK  | MM   |

NOTES:




1. MATERIALS:
  - HOLDER: PBT, COLOR: NATURAL,
  - CONTACTS: COPPER ALLOY, Ni/Au PLATING.
2. FOR SOLID, FUSED AND STRANDED WIRE TYPES AWG 18 AND 20 ACC. UL 1007.
3. WIRE STRIP LENGTH: 11-12 mm
4. MAX. WIRE INSULATION OUTER DIAM.:  $\varnothing 2.3\text{mm}$ .
5. RECOMMENDED SCREW TORQUE: 0.4 - 0.6 Nm.
6. SCREWS TO BE USED:
  - PAN HEAD M3, #4-40 AND COUNTERSUNC M3 (2x), SEE TABLE SHEET 2.
7. FOR LED THICKNESS RANGE 0.9-1.0 NOM.
8. LED MATING ON 2 CORNERS WITH ADHESIVE TAPE.

- 9


SPECIAL PACKAGING IN 20 PIECES TRAY AND BAGGED IN GROUPS OF 100 PIECES.
10. FOR COB-TO-HOLDER CROSS REFERENCE, REFER TO APPLICATION SPECIFICATION 114-32208.





P/N 2213678-3  
AS SHOWN



P/N 2213678-4  
AS SHOWN



SECTION X-X



|                                                                                                               |  |                                 |                                                                                                       |  |                         |                 |
|---------------------------------------------------------------------------------------------------------------|--|---------------------------------|-------------------------------------------------------------------------------------------------------|--|-------------------------|-----------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                                        |  | DWN<br>P. POORTER<br>22MAY2015  |  TE Connectivity |  |                         |                 |
| DIMENSIONS:<br>mm                                                                                             |  | CHK<br>O. LEIJNSE<br>22MAY2015  |                                                                                                       |  |                         |                 |
| TOLERANCES UNLESS OTHERWISE SPECIFIED:                                                                        |  | APVD<br>O. LEIJNSE<br>22MAY2015 | NAME<br>MINI COB HOLDER PLATFORM                                                                      |  |                         |                 |
| 0 PLC $\pm 0.2$<br>1 PLC $\pm 0.2$<br>2 PLC $\pm 0.1$<br>3 PLC $\pm 0.1$<br>4 PLC $\pm 0.1$<br>ANGLES $\pm 5$ |  | PRODUCT SPEC<br>108-133062      | SIZE<br>A2                                                                                            |  |                         |                 |
| MATERIAL                                                                                                      |  | APPLICATION SPEC<br>114-133062  | CAGE CODE<br>00779                                                                                    |  | DRAWING NO<br>C-2213678 | RESTRICTED TO   |
| FINISH                                                                                                        |  | WEIGHT                          | CUSTOMER DRAWING                                                                                      |  | SCALE<br>1:1            | SHEET<br>1 OF 3 |
|                                                                                                               |  |                                 |                                                                                                       |  | REV<br>D                |                 |

| REVISIONS |     |             |      |     |      |
|-----------|-----|-------------|------|-----|------|
| P         | LTR | DESCRIPTION | DATE | DWN | APVD |
|           | -   | SEE SHEET 1 | -    | -   | -    |
|           |     |             |      |     |      |
|           |     |             |      |     |      |
|           |     |             |      |     |      |

D

D

C

C

B

B



A

A


LED OUTLINE:  
P/N 2-2213678-3  
P/N 1-2213678-4 (NO TAPE)  
P/N 1-2213678-3 (NO TAPE)  
P/N 2213678-3  
P/N 2213678-4 (SHOWN)

LED OUTLINE:  
P/N 1-2213678-6 (NO TAPE)  
P/N 1-2213678-5 (NO TAPE)  
P/N 2213678-5  
P/N 2-2213678-5  
P/N 2213678-6 (SHOWN)

P/N 3-2213678-3  
P/N 3-2213678-4



|              |                |             |                 |             |             |      |            |
|--------------|----------------|-------------|-----------------|-------------|-------------|------|------------|
| 400          | 20             | 4-2213678-5 | 35mm LED Holder | 12*15       | PAN HEAD    | YES  | YES        |
| 400          | 20             | 4-2213678-3 | 35mm LED Holder | 13.5*13.5   | PAN HEAD    | YES  | YES        |
| 1050         | 35             | 3-2213678-4 | 35mm LED Holder | 12*15       | COUNTERSUNK | YES  | YES        |
| 1050         | 35             | 3-2213678-3 | 35mm LED Holder | 12*15       | PAN HEAD    | YES  | YES        |
| 500          | 20             | 2-2213678-6 | 35mm LED Holder | 13.5*13.5   | PAN HEAD    | YES  | YES        |
| 500          | 20             | 2-2213678-5 | 35mm LED Holder | 13.5*13.5   | PAN HEAD    | YES  | YES        |
| 300          | 10             | 2-2213678-3 | 35mm LED Holder | 12*15       | PAN HEAD    | YES  | YES        |
| 1050         | 35             | 1-2213678-6 | 35mm LED Holder | 13.5*13.5   | COUNTERSUNK | NO   | YES        |
| 1050         | 35             | 1-2213678-5 | 35mm LED Holder | 13.5*13.5   | PAN HEAD    | NO   | ON REQUEST |
| 1050         | 35             | 1-2213678-4 | 35mm LED Holder | 12*15       | COUNTERSUNK | NO   | ON REQUEST |
| 1050         | 35             | 1-2213678-3 | 35mm LED Holder | 12*15       | PAN HEAD    | NO   | YES        |
| 1050         | 35             | 2213678-6   | 35mm LED Holder | 13.5*13.5   | COUNTERSUNK | YES  | YES        |
| 1050         | 35             | 2213678-5   | 35mm LED Holder | 13.5*13.5   | PAN HEAD    | YES  | YES        |
| 1050         | 35             | 2213678-4   | 35mm LED Holder | 12*15       | COUNTERSUNK | YES  | YES        |
| 1050         | 35             | 2213678-3   | 35mm LED Holder | 12*15       | PAN HEAD    | YES  | YES        |
| SHIPPING QTY | PARTS PER TRAY | PART NO     | DESCRIPTION     | LED OUTLINE | SCREW TYPE  | TAPE | AVAILABLE  |



THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN  
P. POORTER  
CHK  
O. LEIJNSE  
APVD  
O. LEIJNSE

22MAY2015  
22MAY2015  
22MAY2015

DIMENSIONS:  
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ±0.2  
1 PLC ±0.2  
2 PLC ±0.1  
3 PLC ±0.1  
4 PLC ±0.1  
ANGLES ±5  
FINISH

MATERIAL

-

STE

TE Connectivity

NAME  
MINI COB HOLDER PLATFORM

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
C-2213678

RESTRICTED TO

SCALE  
2:1

SHEET  
2 OF 3

REV  
D

CUSTOMER DRAWING

SCALE  
2:1

SHEET  
2 OF 3

REV  
D

1471-9 (3/13)  
Downloaded from Arrow.com

